

# Product data sheet

Specifications



Thermistor probe, TeSys LT3,  
integrated triple probe, 170°C, 0 to  
2.5V, bulk qty

DA1TT170

## Main

Range Of Product	DA1
Product Or Component Type	Thermistor probe
Device Short Name	DA1TT
Accessory / Separate Part Category	Protection accessory
Quantity Per Set	Set of 10
Ambient Air Temperature For Operation	170 °C

## Complementary

[Ui] Rated Insulation Voltage	2500 V
[Ue] Rated Operational Voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable Length	1 m between probe and motor terminal plate 250 mm between probes
Net Weight	0.01 kg

## Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	9.0 cm
Package 1 Length	12.5 cm
Package 1 Weight	9.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	1.5 cm
Package 2 Width	9.0 cm
Package 2 Length	12.5 cm
Package 2 Weight	93.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.03 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>