

# Product data sheet

Specifications



Empty enclosures for standard starters, TeSys LE, without pushbuttons, for LE1D18-D35

DE1DS2A04

## Main

Range Of Product	TeSys
Range	TeSys
Device Short Name	DE1D
Product Or Component Type	Enclosure
Material	Polycarbonate
Device Composition	Contacteur ordered separately Thermal overload relay ordered separately
Product Compatibility	LE1D18...35
Control Type	Without

## Complementary

Cable Entry Number	2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom
Height	201 mm
Width	103 mm
Depth	145 mm
Net Weight	0.5 kg

## Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 60529
Ambient Air Temperature For Operation	-5...40 °C
Environmental Characteristic	Standard environment
Product Certifications	UKCA

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	16.500 cm
Package 1 Length	25.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	786.000 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	22
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	29.852 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>