

# Product data sheet

Specifications



## 10A 250V 1G Switched 2 Universal Pin + 3 Flat Pin China Socket, Lavendar Silver

E8215\_10US\_LS

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

### Main

Product Or Component Type	Socket-outlet
Switch Function	Switch
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	No inductive load
Cover Frame Colour Tint	Lavender silver

### Complementary

Wiring Device Mounting	Flush Surface
Outlet Poles Configuration	2P + E china 2P universal
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Switch: pillar terminals Socket: clamp terminal
Clamping Connection Capacity	2 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	8.8 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	GB 16915.1-2003 GB 2099.1-2008

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.29 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	87.1 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	967.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.282 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations