

# Product data sheet

Specifications



## Cover plate, AvatarOn, for switched socket, 13A, 3P, white

E8315C\_WE\_C5

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Product Or Component Type	Cover plate
Accessory / Separate Part Category	Mounting accessory
Colour Tint	White painted
Type Of Packing	Flow-pack
Outlet Poles Configuration	3P
Outlet Standard	British BS 1363A
Main Colour Tint	White

### Complementary

Colour Tint	White
Range Compatibility	AvatarOn switched socket
Product Destination	Switched socket
Socket Number	1
Number Of Rocker	1
[In] Rated Current	13 A
Material	PC (polycarbonate)
Surface Finish	Glossy
Surface Treatment	Untreated
Height	86 mm
Width	86 mm
Depth	21 mm

### Environment

Ambient Air Temperature For Storage	-5...45 °C
Ambient Air Temperature For Operation	0...95 °C
Standards	IEC 60670 BS 5733

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	83.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	15
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.284 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	90
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	8204.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations