

# Product data sheet

Specifications



## Double USB charger + switched socket, AvatarOn, 3P, 13A, Wood

E8315USB\_WD\_C5

### Main

Product Or Component Type	USB charger + switched socket
Fixing Mode	By screws

### Complementary

Outlet Standard	British
Outlet Standard Description	With earthing contact
Integrated Connection Type	2 USB type A 5 V DC 2.1 A 1 socket-outlet 250 V AC 13 A 50/60 Hz
Device Mounting	Surface
Device Presentation	Complete product
Mounting Support	Mounting box
Outlet Poles Configuration	3P with shutter
Colour Tint	Wood
Surface Finish	Matt
Surface Treatment	Painted
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...60 °C
Protection Type	Current protection Thermal protection
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	0...40 °C
Service Life In Cycles	5000 cycles
Connections - Terminals	Screw terminal
Number Of Terminals	3
Screwdriver Shape	Phillips combined
Number Of Cables	2
Clamping Connection Capacity	1.5...4 mm² for rigid cable(s) 1.5...4 mm² for stranded cable(s) 1.5...4 mm² for flexible cable(s)
Material	PC (polycarbonate): grid plate PC (polycarbonate): surround
Wire Stripping Length	12 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	86 mm
Width	86 mm
Depth	38.2 mm
Embedding Depth	29.3 mm
Standards	UL 94 UL 1310 UL 498

## Environment

Ip Degree Of Protection	IP20
-------------------------	------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	109.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.263 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>