

Product data sheet

Specifications



Momentary Switch, AvatarOn, 4A, 250V, 1gang, White

E8331PRL1_WE_G11

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	AvatarOn
Product Or Component Type	Time delay switch
Device Presentation	Complete product

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Rocker	1
Actuator	Rocker
Fixing Mode	Clip-in
Colour Tint	White
Surface Finish	Glossy
[Ie] Rated Operational Current	Resistive: 4 A Inductive: 4 A
[Ue] Rated Operational Voltage	250 V AC 50...60 Hz
Clamping Connection Capacity	1...4 mm ² for rigid cable(s) 1...4 mm ² for stranded cable(s) 1...4 mm ² for flexible cable(s)
Wire Stripping Length	12 mm
Material	PC (polycarbonate): base PC (polycarbonate): base cover PC (polycarbonate): grid plate PC (polycarbonate): surround PC (polycarbonate): dolly Brass: terminal cover
Height	86 mm
Width	86 mm
Depth	34 mm
Embedding Depth	25 mm
Net Weight	0.077 kg

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	77.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	842.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

 Sustainable Packaging

Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations