


# Product data sheet

Specifications



## 10A 1 Gang 3 Flat Pin Switched Socket with Shutter and Ondicator, Wine Gold

E8415\_10S\_GA\_WG

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Power socket-outlet
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E China
Load Type	Resistive
Colour Tint	Wine gold
Cover Frame Colour Tint	White

### Complementary

Device Mounting	Surface Flush
Local Signalling	Mechanical indicator
Switch Function	Push-button
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Connections - Terminals	Brass pillar Clamps terminal
Embedding Depth	23.8 mm
Width	87 mm
Height	87 mm
Depth	32 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	GB 2099.1 GB 16915.1
Standards	GB 2099.1 GB 16915.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	88.2 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	<a href="#">End of Life Information</a>