


# Product data sheet

Specifications



## 16AX/20A 2 Gang 2 Way Full-Flat Switch, Black

E8432\_2\_GA\_DG

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Fluorescent lamp Incandescent lamp Resistive Inductive
Colour Tint	Black
Cover Frame Colour Tint	Black

### Complementary

Device Mounting	Surface Flush
Switch Function	2-way
Rated Current	20 A at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Number Of Gangs	2 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	EN 60669-1 MS IEC 60669-1 GB 16915.1 IEC 60669-1 SS 227-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.24 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	82.2 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	919.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.5 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.994 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations