

# Product data sheet

Specifications



## Telephone socket, AvatarOn, metal gold hairline

E8331RJS4\_GH\_G11

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Product Or Component Type	Telephone socket
Device Application	Communication
Socket Additional Information	Shuttered
Number Of Gangs	1 gang
Material	PC (polycarbonate): housing Polycarbonate: plastic part
Colour Tint	Metal gold hairline
Colour Tint	Metal gold hairline

### Complementary

Device Presentation	Complete product
Device Mounting	Surface Flush
Communication Network Category	Voice: 3
Rated Current	1.5 A
Contacts Material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Contact Resistance	1 $\mu$ Ohm
Insulation Resistance	$\geq$ 200 MOhm
Minimum Return Loss	23 dB
Width	86 mm
Height	86 mm
Depth	40.7 mm

### Environment

Dielectric Strength	1000 V for 60 s at 60 Hz
Awg Gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental Characteristic	UV resistant
Maximum Ambient Air Temperature For Operation	45 °C
Relative Humidity	0...95 %
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
-------------------------	------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	58 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	638 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	3.828 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations