


# Product data sheet

Specifications



## Momentary Switch, AvatarOn, 4A, 250V, 3gangs, Wine Gold

E8333PRL1\_WG\_C5

### Main

Range	AvatarOn
Product Or Component Type	Time delay switch
Device Presentation	Complete product

### Complementary

Device Mounting	Flush
Number Of Gangs	3 gangs
Number Of Rocker	3
Actuator	Rocker
Fixing Mode	Clip-in
Colour Tint	Wine gold
Surface Finish	Glossy
[Ie] Rated Operational Current	Resistive: 4 A Inductive: 4 A
[Ue] Rated Operational Voltage	250 V AC 50...60 Hz
Clamping Connection Capacity	1...4 mm² for rigid cable(s) 1...4 mm² for stranded cable(s) 1...4 mm² for flexible cable(s)
Wire Stripping Length	12 mm
Material	PC (polycarbonate): base PC (polycarbonate): base cover PC (polycarbonate): grid plate PC (polycarbonate): surround PC (polycarbonate): dolly Brass: terminal cover
Height	86 mm
Width	86 mm
Depth	34 mm
Embedding Depth	25 mm
Net Weight	0.11 kg

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	89.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	984.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations