

Product data sheet

Specifications



Asfora - 1pole pushbutton -10A lift terminals, locator light, cream

EPH1600323

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Asfora
Product Or Component Type	Push-button
Device Presentation	Complete product
Number Of Rocker	1
Colour Tint	Cream
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Local Signalling	LED
Power Range	2300 W
Rated Current	10 A at 250 V AC
Number Of Cables	2 cable(s) 2.5 mm²
Cable Stiffness	Flexible Rigid Solid stranded
Wire Stripping Length	13.0 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface Finish	Glossy
Conductor Material	Copper
Fixing Mode	Screws or claws51...70 mm
Connections - Terminals	Lift terminals
Width	83 mm
Height	83 mm
Depth	43.0 mm
Projecting Depth	15 mm
Net Weight	0.0759 kg

Environment

Standards	IEC 60669-1
Product Certifications	VDE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quality Labels	CE
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.3 cm
Package 1 Width	8.3 cm
Package 1 Length	4.3 cm
Package 1 Weight	86.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.4 cm
Package 2 Width	18.5 cm
Package 2 Length	27.5 cm
Package 2 Weight	999.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	12.739 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations