

# Product data sheet

Specifications



## Mureva BOX - security junction box - knock-out - 150x105x80 mm

ENN05177

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Product Range	Mureva BOX
Product Type	Junction box for security circuits
Quantity Per Package	1 piece

### Complementary

Mounting	Surface
Cable Entry	Knock-out
Fixing Mode	Screw-fixed: cover
Inner Dimensions	150 x 105 x 80 mm
Number Of Cable Entries	4 x M16/20 8 x M12/16 2 x M20/25
Material	PP (polypropylene): body and cover
Electrical Insulation Class	Class II conforming to IEC 536
Height	87 mm
Width	171 mm
Depth	128 mm
Net Weight	0.23 kg

### Environment

Operating Temperature	-25...40 °C
Ip-Class	IP55 conforming to IEC 60529
Ik-Class	IK07 conforming to EN 50102
Glow Wire Temperature	960 °C
Standards	EN 60670 CE
Environmental Characteristic	Slightly halogenated

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10.5 cm
Package 1 Length	15 cm
Package 1 Weight	230 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	40
Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.34 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1000
Package 3 Height	220 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	280 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations