

Product data sheet

Specifications



Mureva BOX - security junction box - 7 grommets Ø20 - 80x80x45 mm

ENN05264

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Range	Mureva BOX
Product Type	Junction box for security circuits
Quantity Per Package	5 pieces

Complementary

Mounting	Surface
Cable Entry	Grommets
Fixing Mode	Clip-on: cover
Inner Dimensions	80 x 80 x 45 mm
Number Of Cable Entries	7 diameter: 20 mm
Material	PP (polypropylene): body and cover SBS (styrene butadiene styrene): grommet
Electrical Insulation Class	Class II conforming to IEC 536
Height	51 mm
Width	98 mm
Depth	98 mm
Net Weight	0.088 kg

Environment

Operating Temperature	-25...40 °C
Ip-Class	IP55 conforming to IEC 60529
Ik-Class	IK07 conforming to EN 50102
Glow Wire Temperature	960 °C
Standards	EN 60670 CE
Environmental Characteristic	Slightly halogenated

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8 cm
Package 1 Weight	88 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9 cm
Package 2 Width	9 cm
Package 2 Length	25.5 cm
Package 2 Weight	440 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	28 cm
Package 3 Width	40 cm
Package 3 Length	52.5 cm
Package 3 Weight	9.064 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--------------------------------------------

Environmental Disclosure	Product Environmental Profile
--------------------------	-----------------------------------------------

Circularity Profile	No need of specific recycling operations
---------------------	------------------------------------------