

Product data sheet

Specifications



Asfora, SAT socket ending, 1dB, cream

EPH3700123

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Asfora
Product Or Component Type	SAT socket
Device Presentation	Complete product
Tv Socket Type	End-of-line (terminal socket)
Wiring Device Additional Information	For series distribution systems For parallel distribution systems
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Fixing Mode	Claws51...80 mm
Socket Number	1
Sat Connector	F type
Attenuation	1 dB
Colour Tint	Cream
Surface Finish	Glossy
Material	ABS (acrylonitrile butadiene-styrene): central plate ABS (acrylonitrile butadiene-styrene): cover frame
Dc Current Flow	In SAT socket
Number Per Line	1
Connections - Terminals	Screwless terminals
Conductor Material	Copper
Height	83 mm
Width	83 mm
Depth	42 mm
Projecting Depth	13 mm
Net Weight	0.087 kg
Ip Degree Of Protection	IP20

Environment

Quality Labels	CE
----------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	16.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	90.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.1 cm
Package 2 Width	18.5 cm
Package 2 Length	27.5 cm
Package 2 Weight	1.039 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	13.219 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations