


Product data sheet

Specifications



Asfora -1pole pushbutton with locator light, screw terminals,wo frame, aluminium

EPH1600361

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Asfora
Product Or Component Type	Push-button
Device Presentation	Mechanism with fixing frame
Number Of Rocker	1
Colour Tint	Aluminium
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Local Signalling	LED
Power Range	2300 W
Rated Current	10 A at 250 V AC
Number Of Cables	2 cable(s) 2.5 mm²
Cable Stiffness	Flexible Rigid Solid stranded
Wire Stripping Length	13.0 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface Finish	Painted
Conductor Material	Copper
Fixing Mode	Screws or claws51...70 mm
Connections - Terminals	Lift terminals
Width	71 mm
Height	71 mm
Depth	43.0 mm
Projecting Depth	15 mm
Net Weight	0.0639 kg

Environment

Standards	IEC 60669-1
Product Certifications	VDE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quality Labels	CE
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	7.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	63.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	713.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.181 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations