

Product data sheet

Specifications



Asfora - single socket outlet - pin earth - cream

EPH2801123

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

Main

| | |
|----------------------------|---------------------------|
| Range | Asfora |
| Product Or Component Type | Socket-outlet |
| Socket Number | 1 |
| Outlet Poles Configuration | 2P + E |
| Colour Tint | Cream |
| Type Of Packing | Flow-pack with inlay card |

Complementary

| | |
|-----------------------------|---|
| Device Presentation | Complete product |
| Device Mounting | Flush |
| Fixing Mode | Screws or claws51...69 mm |
| Outlet Standard | CEE 7/5 |
| Outlet Standard | French |
| Outlet Standard Description | Pin earth |
| Power Range | 3680 W |
| Rated Current | 16 A at 250 V AC |
| Surface Finish | Glossy |
| Material | ABS (acrylonitrile butadiene-styrene): cover frame ABS + PC: central plate |
| Wire Stripping Length | 13.0 mm |
| Conductor Material | Copper |
| Connections - Terminals | Lift terminals |
| Number Of Cables | 3 cable(s) 2.5 mm² |
| Cable Stiffness | Flexible Rigid Solid stranded |
| Quantity Per Set | 1 |
| Ip Degree Of Protection | IP20 |
| Projecting Depth | 10 mm |
| Width | 83 mm |
| Height | 83 mm |
| Depth | 42 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------|----------|
| Net Weight | 0.081 kg |
|------------|----------|

Environment

| | |
|------------------------|----------------|
| Standards | IEC 60884-1 |
| Product Certifications | SEP-BBJ TSE |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.3 cm |
| Package 1 Width | 8.3 cm |
| Package 1 Length | 4.2 cm |
| Package 1 Weight | 81 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 9.1 cm |
| Package 2 Width | 18.5 cm |
| Package 2 Length | 27.5 cm |
| Package 2 Weight | 800 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 96 |
| Package 3 Height | 30 cm |
| Package 3 Width | 40 cm |
| Package 3 Length | 60 cm |
| Package 3 Weight | 10.26 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |