

Product data sheet

Specifications



Asfora - single socket outlet with side earth with shutters, wo frame, aluminium

EPH2900261

Main

| | |
|-------------------------------|---------------|
| Range | Asfora |
| Product Or Component Type | Socket-outlet |
| Socket Number | 1 |
| Outlet Poles Configuration | 2P + E |
| Socket Additional Information | Shuttered |
| Colour Tint | Aluminium |
| Type Of Packing | Flow-pack |

Complementary

| | |
|-----------------------------|-------------------------------------|
| Device Presentation | Mechanism with fixing frame |
| Device Mounting | Flush |
| Fixing Mode | Screws or claws51...69 mm |
| Outlet Standard | CEE 7/3 |
| Outlet Standard | Schuko |
| Outlet Standard Description | Side earth |
| Power Range | 3680 W |
| Rated Current | 16 A at 250 V AC |
| Surface Finish | Painted |
| Material | ABS + PC: central plate |
| Wire Stripping Length | 13.0 mm |
| Conductor Material | Copper |
| Connections - Terminals | Lift terminals |
| Number Of Cables | 2 cable(s) 2.5 mm² |
| Cable Stiffness | Flexible Rigid Solid stranded |
| Quantity Per Set | 1 |
| Ip Degree Of Protection | IP20 |
| Projecting Depth | 10 mm |
| Width | 71 mm |
| Height | 71 mm |
| Depth | 42 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------|----------|
| Net Weight | 0.069 kg |
|------------|----------|

Environment

| | |
|------------------------|---------------------|
| Standards | IEC 60884-1 |
| Product Certifications | TSE VDE AENOR |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.7 cm |
| Package 1 Width | 8.4 cm |
| Package 1 Length | 9.4 cm |
| Package 1 Weight | 72.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.4 cm |
| Package 2 Width | 18.5 cm |
| Package 2 Length | 27.5 cm |
| Package 2 Weight | 785.0 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 120 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 40.0 cm |
| Package 3 Length | 60.0 cm |
| Package 3 Weight | 10.123 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |