

Product data sheet

Specifications



Asfora - double socket outlet with pin earth - 16A white, PL std

EPH9800221

Main

Range	Asfora
Product Or Component Type	Socket-outlet
Socket Number	2
Outlet Poles Configuration	2P + E
Colour Tint	White
Type Of Packing	Flow-pack

Complementary

Device Presentation	Complete product
Device Mounting	Flush
Fixing Mode	Claws54...72 mm
Outlet Standard	CEE 7/5
Outlet Standard	French
Outlet Standard Description	Pin earth
Power Range	3680 W
Rated Current	16 A at 250 V AC
Surface Finish	Glossy
Material	ABS (acrylonitrile butadiene-styrene): cover frame ASA + PC: central plate
Wire Stripping Length	11 mm
Conductor Material	Copper
Connections - Terminals	Lift terminals
Number Of Cables	2 cable(s) 2.5 mm²
Cable Stiffness	Rigid Flexible Solid stranded
Quantity Per Set	1
Ip Degree Of Protection	IP20
Projecting Depth	23 mm
Width	83 mm
Height	123 mm
Depth	46 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60884-1
Product Certifications	B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	8.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	102.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.000 cm
Package 2 Width	20.000 cm
Package 2 Length	31.000 cm
Package 2 Weight	1.126 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	50
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	5.977 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

 Sustainable Packaging

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations