

# Product data sheet

Specifications



## Asfora, TV-R-SAT ending socket, 1dB, bronze

EPH3500169

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                                      |  |
|--------------------------------------|--|
| Range                                | Asfora   |
| Product Or Component Type            | TV/SAT/R socket  |
| Device Presentation                  | Mechanism with fixing frame  |
| Tv Socket Type                       | End-of-line (terminal socket)  |
| Wiring Device Additional Information | For parallel distribution systems<br>For series distribution systems |
| Type Of Packing                      | Flow-pack  |

### Complementary

|                         |  |
|-------------------------|--|
| Device Mounting         | Flush  |
| Fixing Mode             | Claws51...80 mm                                      |
| Socket Number           | 3  |
| Tv Connector            | Male IEC 9.52 mm                                     |
| Radio Connector         | Female IEC 9.52 mm                                   |
| Sat Connector           | F type   |
| Attenuation             | 1 dB   |
| Colour Tint             | Bronze   |
| Surface Finish          | Painted  |
| Material                | ABS (acrylonitrile butadiene-styrene): central plate |
| Dc Current Flow         | In SAT socket  |
| Number Per Line         | 1  |
| Connections - Terminals | Screwless terminals                                  |
| Conductor Material      | Copper   |
| Height                  | 71 mm  |
| Width                   | 71 mm  |
| Depth                   | 42 mm  |
| Projecting Depth        | 13 mm  |
| Net Weight              | 0.105 kg   |
| Ip Degree Of Protection | IP20   |

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |    |
|----------------|----|
| Quality Labels | CE |
|----------------|----|

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 16 cm   |
| Package 1 Width              | 11 cm   |
| Package 1 Length             | 5 cm    |
| Package 1 Weight             | 108 g   |
| Unit Type Of Package 2       | BB1     |
| Number Of Units In Package 2 | 10      |
| Package 2 Height             | 9.4 cm  |
| Package 2 Width              | 18.5 cm |
| Package 2 Length             | 27.5 cm |
| Package 2 Weight             | 1180 kg |
| Unit Type Of Package 3       | S03     |
| Number Of Units In Package 3 | 60      |
| Package 3 Height             | 30 cm   |
| Package 3 Width              | 30 cm   |
| Package 3 Length             | 40 cm   |
| Package 3 Weight             | 7567 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|   |   |   |
|---|---|---|
|  | Toxic Heavy Metal Free  |   |
|  | Mercury Free  |   |
|  | Rohs Exemption Information  | <a href="#">Yes</a>   |
| <b>Eu Rohs Directive</b>  | Compliant   | <a href="#">EU RoHS Declaration</a>                               |
| <b>China Rohs Regulation</b>  | <a href="#">China RoHS declaration</a>  | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| <b>Weee</b>   | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |   |