

Product data sheet

Specifications



Asfora - double socket-outlet with side earth contact, anthracite

EPH9900171

Main

| | |
|----------------------------|---------------|
| Range | Asfora |
| Product Or Component Type | Socket-outlet |
| Socket Number | 2 |
| Outlet Poles Configuration | 2P + E |
| Colour Tint | Anthracite |
| Type Of Packing | Flow-pack |

Complementary

| | |
|-----------------------------|---|
| Device Presentation | Complete product |
| Device Mounting | Flush |
| Fixing Mode | Claws54...72 mm |
| Outlet Standard | CEE 7/3 |
| Outlet Standard Deviation | Schuko |
| Outlet Standard Description | Side earth |
| Power Range | 3680 W |
| Rated Current | 16 A at 250 V AC |
| Surface Finish | Painted |
| Material | ABS (acrylonitrile butadiene-styrene): cover frame ASA + PC: central plate |
| Wire Stripping Length | 11 mm |
| Conductor Material | Copper |
| Connections - Terminals | Lift terminals |
| Number Of Cables | 2 cable(s) 2.5 mm² |
| Cable Stiffness | Flexible Solid stranded Rigid |
| Quantity Per Set | 1 |
| Ip Degree Of Protection | IP20 |
| Projecting Depth | 23 mm |
| Width | 83 mm |
| Height | 123 mm |
| Depth | 46 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|------------------------|---------------------|
| Standards | IEC 60884-1 |
| Product Certifications | AENOR VDE UKR |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.500 cm |
| Package 1 Width | 8.500 cm |
| Package 1 Length | 12.500 cm |
| Package 1 Weight | 102.200 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 10.000 cm |
| Package 2 Width | 20.000 cm |
| Package 2 Length | 31.000 cm |
| Package 2 Weight | 1.123 kg |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 50 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 40.000 cm |
| Package 3 Length | 60.000 cm |
| Package 3 Weight | 5.960 kg |

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |