

Product data sheet

Specifications



Ultra - adjustable internal corner - 16 x 16 mm - ABS - white

ETK16320

Main

| | |
|---------------------------|---------------------------------|
| Range Of Product | Ultra |
| Product Or Component Type | Internal corner |
| Device Application | Cable distribution |
| Colour Tint | White (RAL 9010) |
| Quantity Per Set | Set of 60 |
| Market Segment | Small commercial Residential |

Complementary

| | |
|--------------------|-----------------------------|
| Trunking Dimension | 16 x 16 mm |
| Trunking Material | Plastic |
| Adjustment | Adjustable |
| Fixing Mode | Snap-fitted |
| Material | ABS thermoplastic enclosure |
| Height | 16 mm |
| Width | 35 mm |
| Depth | 32 mm |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Standards | EN 50085-1:2005 EN 50085-2-1:2006 |
| Ambient Air Temperature For Operation | -5...60 °C |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.2 cm |
| Package 1 Width | 1.6 cm |
| Package 1 Length | 3.5 cm |
| Package 1 Weight | 3 g |
| Unit Type Of Package 2 | BB1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|---------|
| Number Of Units In Package 2 | 60 |
| Package 2 Height | 13 cm |
| Package 2 Width | 14 cm |
| Package 2 Length | 17 cm |
| Package 2 Weight | 257 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 960 |
| Package 3 Height | 30 cm |
| Package 3 Width | 40 cm |
| Package 3 Length | 60 cm |
| Package 3 Weight | 4.51 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|-----------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile | No need of specific recycling operations |