

Product data sheet

Specifications



Easy9 - comb busbar - 3L - 18 mm pitch - 12 modules - 80A

EZ9X33312

Main

Range	Easy9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	4 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	18 mm
Connector Type	Tooth
Distance Between Way	54 mm
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	80 A at 40 °C
[Ue] Rated Operational Voltage	230 V AC Ph/N 400 V AC Ph/Ph
[Ui] Rated Insulation Voltage	500 V AC conforming to IEC 61439-1
Mounting Location	Top or bottom on tunnel type terminals
9 Mm Pitches	24
Width	220 mm
Colour	Light grey (RAL 7035)
Range Compatibility	Easy9 Easy9 MCB Easy9 Easy9 RCBO Easy9 Easy9 RCCB Easy9 Easy9 switch

Environment

Standards	IEC 60947-7-1 IEC 61439-1 IEC 60664
Product Certifications	CE
Fire Resistance	850 °C (30 s) conforming to IEC 60695-2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution Degree	3 conforming to IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.2 cm
Package 1 Width	1.0 cm
Package 1 Length	2.5 cm
Package 1 Weight	0.114 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations