

# Product data sheet

Specifications



## Ultra - stop end - 21 x 12 mm - ABS - white

ETK20560

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                           |                                 |
|---------------------------|---------------------------------|
| Range Of Product          | Ultra                           |
| Product Or Component Type | Stop end                        |
| Colour Tint               | White (RAL 9010)                |
| Quantity Per Set          | Set of 20                       |
| Market Segment            | Residential<br>Small commercial |

### Complementary

|                       |                             |
|-----------------------|-----------------------------|
| Product Compatibility | Cable distribution          |
| Trunking Dimension    | 21 x 12 mm                  |
| Trunking Material     | Plastic                     |
| Fixing Mode           | Snap-fitted                 |
| Material              | ABS thermoplastic enclosure |
| Height                | 7 mm                        |
| Width                 | 23 mm                       |
| Depth                 | 13 mm                       |

### Environment

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| Standards                             | EN 50085-1:2005<br>EN 50085-2-1:2006 |
| Ambient Air Temperature For Operation | -5...60 °C                           |
| Ip Degree Of Protection               | IP40                                 |
| Ik Degree Of Protection               | IK07                                 |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 1.3 cm |
| Package 1 Width              | 0.7 cm |
| Package 1 Length             | 2.3 cm |
| Package 1 Weight             | 2.0 g  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

|                       |   |
|-----------------------|---|
| Reach Regulation      | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive     | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile   | No need of specific recycling operations  |