

Product data sheet

Specifications



Ultimate - Switched Socket 2 USB charger - 2 gang - 13A - polished - black

GGBGU34202USBBPC

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Ultimate
Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket with USB charger
Device Presentation	Complete product
Device Application	USB charger
Colour Tint	Front plate: polished brass Interior: black
Surface Finish	Polished
Connections - Terminals	Screw terminals
Switch Function	1-pole
Rated Current	13 A at 220...240 V AC 50/60 Hz

Complementary

Device Mounting	Surface Flush
Outlet Standard	BS 1363
Integrated Connection Type	2 socket-outlet 220...250 V AC 13 A 50/60 Hz 2 USB port 5 V DC 2.1 A
Actuator	Rocker
Number Of Gangs	2 gangs
Pilot Light	Silver without LED
Fixing Mode	2 screw: M3.5 26 mm diameter: 3.5 mm 2 screw: M3.5 32 mm diameter: 3.5 mm
Clamping Connection Capacity	2 x 6 mm² for solid cable(s) 3 x 4 mm² for solid cable(s) 5 x 2.5 mm² for solid cable(s) 3 x 4 mm² for stranded cable(s) 5 x 2.5 mm² for stranded cable(s)
Socket Additional Information	Earthed
Earth Circuit	Standard earth
Material	Stainless steel

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Compatibility	Mobile/tablet Apple Mobile/tablet Samsung Mobile/tablet LG Mobile/tablet Blackberry Mobile/tablet HTC Mobile/tablet Sony Mobile/tablet Huawei Technologies
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2019/1782/EC - ecodesign
Quality Labels	CE
Quantity Per Set	Set of 1
Type Of Packing	Box
Type Of Installation	Indoor
Depth	35 mm
Width	147.5 mm
Height	87.5 mm
Net Weight	0.29 kg

Environment

Ip Degree Of Protection	IP20
Standards	BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	9.7 cm
Package 1 Length	15.5 cm
Package 1 Weight	340 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	17.5 cm
Package 2 Width	43 cm
Package 2 Length	50.5 cm
Package 2 Weight	17.69 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1000
Package 3 Height	104 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	373.8 kg

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Reach Regulation	REACH Declaration
<hr/>	
Eu Rohs Directive	Compliant
	EU RoHS Declaration
<hr/>	
China Rohs Regulation	China RoHS declaration
<hr/>	