

Product data sheet

Specifications



Lisse - Switched Socket - 1 gang - 13A (non standard earth) Satin Brass

GGBL3050NSBSBS

⚠ Discontinued on: Dec 15, 2022

⚠ Discontinued

Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	Switched socket
Device Presentation	Complete product
Outlet Standard	British
Colour Tint	Interior: black Cover plate: satin brass
Socket Additional Information	T-shaped earth pin
Quantity Per Set	Set of 10
Type Of Packing	Bag

Complementary

Switch Function	1-pole
Rated Current	13 A at 250 V AC 50/60 Hz
Actuator	Rocker
Number Of Gangs	1 gang
Pilot Light	without LED
Fixing Mode	Concealed screws
Connections - Terminals	Screw terminals
Material	Stainless steel
Type Of Installation	Indoor
Depth	33 mm
Width	87 mm
Height	87 mm
Net Weight	0.125 kg

Environment

Standards	BS 1363-2
Ip Degree Of Protection	IP20

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	137.2 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.8 cm
Package 2 Width	10 cm
Package 2 Length	20.5 cm
Package 2 Weight	899.6 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	120
Package 3 Height	22 cm
Package 3 Width	43 cm
Package 3 Length	52 cm
Package 3 Weight	18.622 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information