

# Product data sheet

Specifications



## Lisse - Universal Dimmer - 2 gang 2 way LED - 100W/VA Stainless Steel

GGBL6022LSSS

### Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	Dimmer
Device Presentation	Complete product
Load Type	230 V AC LED lamp: 5...100 W Incandescent lamp: 25...100 W Halogen lamp: 25...100 W
Colour Tint	Stainless steel
Quantity Per Set	Set of 1

### Complementary

Device Mounting	Wall mounted
Dimmer Application	Resistive load Inductive load
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Gangs	2 gangs
Material	Stainless steel
Connections - Terminals	Screw terminals
Fixing Mode	Concealed screws
Type Of Packing	Bag
Height	87 mm
Width	87 mm
Depth	44 mm
Net Weight	0.167 kg

### Environment

Standards	BS EN 60669-2-1
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.700 cm
Package 1 Length	8.700 cm
Package 1 Weight	177.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.800 cm
Package 2 Width	10.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	983.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	22.000 cm
Package 3 Width	52.000 cm
Package 3 Length	52.000 cm
Package 3 Weight	20.482 kg

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins