

Product data sheet

Specifications



Lisse - Universal Dimmer - 1 gang 2 way LED - 100W Satin Brass

GGBL6012LSBS

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	Dimmer
Device Presentation	Complete product
Load Type	230 V AC LED lamp: 5...100 W Incandescent lamp: 25...100 W Halogen lamp: 25...100 W
Colour Tint	Satin brass
Quantity Per Set	Set of 1

Complementary

Device Mounting	Wall mounted
Dimmer Application	Inductive load Resistive load
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Gangs	1 gang
Material	Stainless steel
Connections - Terminals	Screw terminals
Fixing Mode	Concealed screws
Type Of Packing	Bag
Height	87 mm
Width	87 mm
Depth	44 mm
Net Weight	0.129 kg

Environment

Standards	BS EN 60669-2-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	144 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.8 cm
Package 2 Width	10 cm
Package 2 Length	25 cm
Package 2 Weight	798.2 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	22 cm
Package 3 Width	52 cm
Package 3 Length	52 cm
Package 3 Weight	16.795 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations