

# Product data sheet

Specifications



## Ultimate - screwless euro modular - 1 gang - black nickel

GU8450BN

### Main

|                           |                        |
|---------------------------|------------------------|
| Range                     | Ultimate               |
| Device Application        | Mounting               |
| Aesthetic Name            | Screwless flat plate   |
| Product Or Component Type | Front plate            |
| Range Compatibility       | Ultimate front plate   |
| Mounting Mode             | Flush-mounted          |
| Colour Tint               | Black nickel brilliant |

### Complementary

|                        |                     |
|------------------------|---------------------|
| Installation Direction | Horizontal/vertical |
| Number Of Gangs        | 1 gang              |
| Fixing Mode            | By screws           |
| Material               | Stainless steel     |
| Quantity Per Set       | Set of 1            |
| Width                  | 88 mm               |
| Height                 | 88 mm               |

### Environment

|                         |      |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 1.5 cm |
| Package 1 Width              | 8.9 cm |
| Package 1 Length             | 8.9 cm |
| Package 1 Weight             | 140 g  |
| Unit Type Of Package 2       | BB1    |
| Number Of Units In Package 2 | 5      |
| Package 2 Height             | 9.2 cm |
| Package 2 Width              | 5.5 cm |
| Package 2 Length             | 9.5 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |         |
|------------------------------|---------|
| Package 2 Weight             | 733 g   |
| Unit Type Of Package 3       | CAR     |
| Number Of Units In Package 3 | 100     |
| Package 3 Height             | 21.5 cm |
| Package 3 Width              | 21.5 cm |
| Package 3 Length             | 30 cm   |
| Package 3 Weight             | 15 kg   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |  |
|--|--|
|  Rohs Exemption Information | Yes                                    |
| Reach Regulation   | <a href="#">REACH Declaration</a>      |
| Eu Rohs Directive  | Compliant with Exemptions              |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a> |