

Product data sheet

Specifications

Linergy FT - Comb busbar - 63 A - 4 tap-offs - 72 mm pitch



GV2G472

Main

Range	Linergy
Product Name	FT
Device Short Name	GV2G
Product Or Component Type	Comb busbar
Accessory / Separate Part Category	Connection accessory
Poles Description	3P
Range Compatibility	TeSys D TeSys GV2 TeSys K TeSys U
Number Of Tap-Offs	4
[Ith] Conventional Free Air Thermal Current	63 A
Connection Pitch	72 mm

Complementary

Mounting Location	On terminal
[U] Rated Insulation Voltage	690 V
Length	260 mm
Net Weight	0.094 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	3.2 cm
Package 1 Length	26 cm
Package 1 Weight	110 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	40
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	4.502 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)


China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

Dimensions Drawings

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



	l	p
GV2G445 (4 x 45 mm)	179	45
GV2G454 (4 x 54 mm)	206	54
GV2G472 (4 x 72 mm)	260	72

Number of tap-offs	a			
	5	6	7	8
GV2G445	224	269	314	359
GV2G454	260	314	368	422
GV2G472	332	404	476	548