

Product data sheet

Specifications



empty enclosure, for TeSys GV2ME,
IP55

GV2MC02

Main

| | |
|------------------------------------|--------------------|
| Range | TeSys |
| Product Or Component Type | Enclosure |
| Device Short Name | GV2MC |
| Accessory / Separate Part Category | Mounting accessory |
| Product Compatibility | GV2ME |
| Enclosure Type | Surface mounting |

Complementary

| | |
|-----------------------------|---------------|
| Auxiliary Mounting Location | Left Right |
| Height | 147 mm |
| Width | 93 mm |
| Depth | 84 mm |
| Net Weight | 0.3 kg |

Environment

| | |
|------------------------------|----------------------|
| Ip Degree Of Protection | IP55 |
| Environmental Characteristic | Standard environment |
| Product Certifications | UKCA |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.000 cm |
| Package 1 Width | 10.000 cm |
| Package 1 Length | 15.500 cm |
| Package 1 Weight | 294.000 g |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 27 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Package 2 Weight | 8.662 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 108 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 45.800 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |