

# GVSCBC7B

## Galaxy VS Classic Battery Cabinet with batteries, IEC, 700mm wide - Config B



### Overview

Description	Battery cabinet that includes batteries and battery breaker.
Model Name	Galaxy VS Classic Battery Cabinet with batteries, IEC, 700mm wide - Config B
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Belarus , Belgium , Benin , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Cayman Islands , Central African Republic , Chad , Chile , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , East Timor , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guinea , French Guiana , Hungary , Iceland , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Qatar , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Yemen , Zambia , Zimbabwe

### Batteries & Runtime

Battery Type	VRLA
Battery mounting	Enclosed battery cabinet

### Physical

Net Weight	748.0 kg
Maximum Height	1970.0 mm
Maximum Width	700.0 mm
Maximum Depth	830.0 mm
Shipping Weight	768.0 kg
Shipping Width	825.0 mm
Shipping Height	2025.0 mm
Shipping Depth	970.0 mm

---

Color	White
-------	-------

---

**Environmental**

---

Operating Environment	0 - 40 °C
Storage Temperature	-15 - 40 °C

---

**Sustainable Offer Status**

---

RoHS	Compliant
REACH	REACH: Contains SVHCs

---