

Product data sheet

Specifications



Mureva BOX - junction box - 7 grommets Ø20 - 80x80x45 mm - White

IMT05024

Main

Range Of Product	Mureva
Product Name	Mureva BOX
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 5

Complementary

Device Mounting	Surface
Fixing Mode	By screw: body housing
Base Dimension	80 x 45 x 80 mm
Cable Entry	Grommets
Cable Entry Number	7 diameter: 20 mm
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover
Height	80 mm
Width	80 mm
Depth	45 mm

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK07
Glow Wire Temp	650 °C
Standards	EN 60670 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8 cm
Package 1 Length	8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	77 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	10 cm
Package 2 Width	10 cm
Package 2 Length	25.5 cm
Package 2 Weight	402 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	53 cm
Package 3 Weight	8.46 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations