

# Product data sheet

Specifications



## Thorsman - Ext. lead 25m HO7RNF 3G2.5 IP44 Contour

IMT33153

### Main

Range	Thorsman
Range Of Product	PROchantier
Product Name	Thorsman cable reel Extended
Product Or Component Type	Extension cable reel
Device Application	Power supply
[Ue] Rated Operational Voltage	230 V
[In] Rated Current	13 A
Colour Tint	Green/black

### Complementary

Outlet Standard	CEE 7/5
Outlet Standard	French
Cable Length	25 m
Cable Cross Section	2.5 mm²
Type Of Cable	H07RN-F3G2.5
Height	295 mm
Width	394 mm
Depth	212 mm
Net Weight	9.04 kg

### Environment

Ip Degree Of Protection	IP44
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.5 cm
Package 1 Width	22.5 cm
Package 1 Length	41.5 cm
Package 1 Weight	9.97 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	108.11 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>