

# Product data sheet

Specifications



## Multifix Air - ceiling box - kit with flush cover and lighting plug E27

IMT35021

### Main

Range Of Product	Multifix
Product Name	Multifix Air
Product Or Component Type	Ceiling box
Device Application	Airtight installation
Device Presentation	With flush cover and lighting plug E27
Provided Equipment	Pre-mounted suspension chimney IPX4 DCL outlet Lighting plug with E27 base DCL plug 2P+E 6A/250 VAC Flush cover Hook
Quantity Per Set	Set of 10

### Complementary

Function Available	Anti-rotation system
Number Of Gangs	1 gang
Fixing Mode	By screws
Material	PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) PP (polypropylene)/TPE (thermoplastic elastomer) ABS (acrylonitrile butadiene-styrene) Steel PA (polyamide) 6.6
Mechanical Robustness	Airtight Fire resistance
Colour Tint	Green (NCS S 2070-G80Y)
Cable Entry	4 knock-out
Drill Diameter/Depth	67 mm 50 mm
Height	71 mm
Width	71 mm
Depth	49 mm

### Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Fire Resistance	850 °C
Standards	EN 60670-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	10.000 cm
Package 1 Length	14.500 cm
Package 1 Weight	104 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	21.000 cm
Package 2 Length	37.500 cm
Package 2 Weight	1.182 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	30
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.190 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations