

# Product data sheet

Specifications



## Mureva Tube GT HF - tee-section - diam.20 - black - LSF0H - IP40

IMT35225

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range Of Product	Mureva Tube GT HF
Product Or Component Type	T-section
Mounting Location	Outdoor Indoor
Nominal Cross Section	74 mm²
Diameter	Internal: 16.8 mm External: 20 mm
Colour Tint	Black (RAL 9005)

### Complementary

Material	PC/ABS
----------	--------

### Environment

Ip Degree Of Protection	IP40
Environmental Characteristic	Non-flame propagating
Product Certifications	NF

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	5 cm
Package 1 Length	5 cm
Package 1 Weight	18 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	13 cm
Package 2 Width	16.5 cm
Package 2 Length	23.5 cm
Package 2 Weight	930 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	250

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	26 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.998 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations