

Product data sheet

Specifications



Thorsman - Cable reel 40m HO5VVF 3G1.5 IP44 Contour

IMT33156

Main

| | |
|--------------------------------|------------------------------|
| Range | Thorsman |
| Range Of Product | PROchantier |
| Product Name | Thorsman cable reel Advanced |
| Product Or Component Type | Extension cable reel |
| Device Application | Power supply |
| [Ue] Rated Operational Voltage | 230 V |
| [In] Rated Current | 13 A |
| Socket Number | 4 |
| Colour Tint | Green/black |

Complementary

| | |
|---------------------|---------------------|
| Outlet Standard | CEE 7/5 |
| Outlet Standard | French |
| Cable Length | 40 m |
| Cable Cross Section | 1.5 mm ² |
| Type Of Cable | H05VV-F3G1.5 |
| Height | 295 mm |
| Width | 376 mm |
| Depth | 201 mm |
| Net Weight | 7.12 kg |

Environment

| | |
|-------------------------|------|
| Ip Degree Of Protection | IP44 |
| Ik Degree Of Protection | IK08 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 23.000 cm |
| Package 1 Width | 35.000 cm |
| Package 1 Length | 42.000 cm |
| Package 1 Weight | 8.680 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|------------|
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 45.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 98.800 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Sustainable Packaging Transparency RoHS/REACH


Resource performance


 Sustainable Packaging

Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)