

# Product data sheet

Specifications



## Multifix Eco - junction box - single

IMT36203

⚠ Discontinued on: Dec 30, 2021

⚠ End-of-service on: Feb 2, 2022

⚠ Discontinued

### Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Eco
Device Short Name	VP-2 K
Product Or Component Type	Junction box
Device Application	Single board
Quantity Per Set	Set of 25

### Complementary

Mounting Mode	Flush-mounted
Device Composition	Stub with locking tabs of stainless steel Adjustable threaded screw ring
Number Of Stubs	2 rigid - diameter: 16 mm
Number Of Combi-Stubs	4 rigid diameter: 16 mm combi-stub(s) 4 rigid diameter: 20 mm combi-stub(s)
Number Of Cross Stubs	2 rigid diameter: 16 mm 2 rigid diameter: 20 mm
Number Of Gangs	1 gang
Material	PEHD (polyethylene high density)
Width	60 mm
Depth	114 mm
Net Weight	0.111 kg
Internal Depth	55 mm
Maximum Cable Cross Section	2.5 mm <sup>2</sup>
Sealing	Without
Surface Treatment	Untreated

### Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.1 cm
Package 1 Width	11.7 cm
Package 1 Length	14.9 cm
Package 1 Weight	100 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations