

Product data sheet

Specifications



Multifix Eco - junction box - single

IMT36204

⚠ Discontinued on: Dec 30, 2021

⚠ Discontinued

Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Eco
Product Or Component Type	Junction box
Device Application	Double board
Quantity Per Set	Set of 25

Complementary

Mounting Mode	Flush-mounted
Device Composition	Stub with locking tabs of stainless steel Adjustable threaded screw ring
Number Of Stubs	2 rigid - diameter: 16 mm
Number Of Combi-Stubs	4 rigid diameter: 16 mm combi-stub(s) 4 rigid diameter: 20 mm combi-stub(s)
Number Of Cross Stubs	2 rigid diameter: 16 mm 2 rigid diameter: 20 mm
Number Of Gangs	1 gang
Material	PEHD (polyethylene high density)
Width	72 mm
Depth	114 mm
Net Weight	0.11 kg
Internal Depth	65 mm
Maximum Cable Cross Section	2.5 mm ²
Sealing	Without
Surface Treatment	Untreated

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	14.3 cm
Package 1 Length	11.3 cm
Package 1 Weight	104 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations