

Product data sheet

Specifications



Multifix Prefal - apparatus box - single - pre-cast - 4 rigid combi stubs - 28mm

IMT36138

 **Discontinued on:** Dec 30, 2021

 **Discontinued**

Main

Range Of Product	Multifix
Product Name	Multifix Prefal
Product Or Component Type	Apparatus box
Device Application	Single board
Quantity Per Set	Set of 50

Complementary

Device Mounting	Flush
Device Composition	Adjustable threaded screw ring Cover Stub with locking tabs of stainless steel
Mounting Support	Board - thickness: 10...27 mm
Number Of Combi-Stub	4 rigid diameter: 16 mm / 20 mm
Number Of Gangs	1 gang
Colour Tint	Grey (NCS 3500)
Material	PEHD (polyethylene high density)
Distance Between Supports	60 mm
Diameter	70 mm
Internal Depth	55 mm
Length	136 mm
Width	58 mm
Depth	71 mm
Net Weight	0.086 kg
Cable Cross Section	2.5 mm ²
Tube Diameter	20 mm
Sealing	With
Connections - Terminals	Snap-on

Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-25...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	7.1 cm
Package 1 Length	13.8 cm
Package 1 Weight	84 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations