

# Product data sheet

Specifications



## Multifix Ceiling - ceiling box - c/c 78 mm - 8 rigid stubs - set of 25

IMT36212

⚠ Discontinued on: Dec 13, 2018

⚠ End-of-service on: Mar 6, 2019

⚠ Discontinued

### Main

|                           |                              |
|---------------------------|------------------------------|
| Range Of Product          | Multifix                     |
| Range                     | Multifix                     |
| Product Name              | Multifix Ceiling             |
| Device Short Name         | JR81                         |
| Product Or Component Type | Ceiling box with rigid stubs |
| Quantity Per Set          | Set of 25                    |

### Complementary

|                             |  |
|-----------------------------|--|
| Device Composition          | Stub with locking tabs of stainless steel<br>Cover                             |
| Number Of Combi-Stub(s)     | 8 rigid diameter: 16 mm combi-stub(s)<br>8 rigid diameter: 20 mm combi-stub(s) |
| Colour Tint                 | Grey   |
| Material                    | Cycoloy 2950   |
| Diameter                    | 95 mm  |
| Distance Between Centers    | 78 mm  |
| Length                      | 156 mm   |
| Width                       | 58 mm  |
| Depth                       | 58 mm  |
| Net Weight                  | 0.199 kg   |
| Connections - Terminals     | Snap-on  |
| Maximum Cable Cross Section | 2.5 mm²  |
| Sealing                     | With   |
| Internal Depth              | 55 mm  |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -25...60 °C |
| Ip Degree Of Protection               | IP20        |

### Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |         |
|------------------|---------|
| Package 1 Height | 15.6 cm |
| Package 1 Width  | 5.8 cm  |
| Package 1 Length | 15.6 cm |
| Package 1 Weight | 199 g   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Certifications & Standards

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**Environmental Disclosure**

[Product Environmental Profile](#)