

# Product data sheet

Specifications



## Multifix TED - ceiling box - recessed - TED-T13

IMT36302

### Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix TED
Device Short Name	TED-T13
Product Or Component Type	Single ceiling box
Device Application	Single board
Quantity Per Set	Set of 50

### Complementary

Device Composition	With stubs located 13 mm from the front edge of the box Cover
Number Of Stubs	2 - diameter: 20 mm 8 - diameter: 16 mm
Colour Tint	Green
Material	PEHD (polyethylene high density) (untreated)
Diameter	83 mm
Length	139 mm
Width	36 mm
Depth	36 mm
Net Weight	0.105 kg
Connections - Terminals	Snap-on
Maximum Cable Cross Section	2.5 mm <sup>2</sup>
Sealing	Without
Internal Depth	34 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	13.000 cm
Package 1 Length	14.300 cm
Package 1 Weight	114.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	29.000 cm
Package 2 Width	38.800 cm
Package 2 Length	58.000 cm
Package 2 Weight	6.282 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	600
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	90.384 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations