

# Product data sheet

Specifications



## Multifix Ceiling - ceiling box 50 mm - c/c 70 mm - 8 integrated stubs

IMT36340

### Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Ceiling
Device Short Name	TB50/SH26
Product Or Component Type	Ceiling box with stubs and knock-outs
Quantity Per Set	Set of 50

### Complementary

Device Composition	With stubs located 26 mm from the front edge of the box Cover
Mounting Support	Hollow wall
Number Of Stubs	2 - diameter: 20 mm 8 - diameter: 16 mm
Cable Entry	2 knock-out for 16 mm bottom conduit 2 knock-out for 20 mm bottom conduit
Colour Tint	Grey
Material	PEHD (polyethylene high density) (untreated)
Diameter	83 mm
Distance Between Centers	70 mm
Length	145 mm
Width	145 mm
Depth	52 mm
Connections - Terminals	Screw terminals
Maximum Cable Cross Section	2.5 mm²
Sealing	Without
Internal Depth	49 mm

### Environment

Ambient Air Temperature For Operation	-25...90 °C
Ip Degree Of Protection	IP30

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	13.1 cm
Package 1 Length	20.3 cm
Package 1 Weight	126 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	50
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	6.814 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations