

# Product data sheet

Specifications



## OptiLine 45 - joint cover piece - PC/ ABS - aluminium metallic

ISM10556

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range Of Product	OptiLine 45
Cabling Installation System	Trunking
Product Type	Joint cover piece
Colour	Aluminium metallic
Quantity Package 1 / Unit	Set of 1

### Complementary

Trunking Material	Aluminium
Trunking Dimension	185 x 55 mm
Fixing Mode	Snap-fitted
Product Material	PC/ABS painted
Length	100 mm
Height	190 mm
Width	57 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19 cm
Package 1 Width	5.7 cm
Package 1 Length	2.4 cm
Package 1 Weight	50 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BAG
Number Of Units In Package 2	65
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	3.406 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	520
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	39.248 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations