

Product data sheet

Specifications



OptiLine 45 - adaptor - aluminium metallic

ISM10957

Main

Cabling Installation System	Post Trunking Pole Service box
Product Or Component Type	Adaptor

Complementary

Type Of Pole	One-sided Two-sided
Type Of Post	Two-sided One-sided
Type Of Service Box	Service box kit
Device Presentation	Empty
Colour Tint	Aluminium metallic
Quantity Per Set	Set of 1
Trunking Material	Aluminium
Trunking Dimension	185 x 55 mm 95 x 55 mm 75 x 55 mm 165 x 55 mm 140 x 55 mm
Product Compatibility	Altira wiring device Unica wiring device
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Free-standing Tension-mounted
Number Of Modules	2 modules
Material	PC + ASA
Length	45 mm
Height	90 mm
Width	72 mm
Market Segment	Residential Small commercial

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7 cm
Package 1 Length	9 cm
Package 1 Weight	62 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.5 cm
Package 2 Width	13 cm
Package 2 Length	18.5 cm
Package 2 Weight	348 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	20
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	1.818 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)