

# Product data sheet

Specifications



## OptiLine 45 - external corner - 140 x 55 mm - PC/ABS - polar white

ISM10302P

### Main

Range Of Product	OptiLine 45
Cabling Installation System	Trunking
Product Type	External corner
Colour	Polar white (RAL 9003)
Quantity Package 1 / Unit	Set of 1

### Complementary

Trunking Material	Plastic
Trunking Dimension	140 x 55 mm
Fixing Mode	Snap-fitted
Product Material	PC/ABS
Length	105 mm
Height	149 mm
Width	105 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	13.000 cm
Package 1 Length	16.000 cm
Package 1 Weight	140.000 g
Unit Type Of Package 2	S03

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.286 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations