

# Product data sheet

Specifications



## OptiLine - minitrunking - 12 x 20 mm - PVC - polar white - with bonding tape - F

ISM14126P

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

### Main

Range Of Product	Optiline
Cabling Installation System	Trunking
Product Type	Mini trunking
Trunking Type	Mini trunking

### Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Colour	White (RAL 9003)
Trunking Dimension	12 x 20 mm
Fixing Mode	Pre-punched fixing hole 100 mm Power cable: screw-fixed Low voltage cable: bonding tape
Material	PVC (polyvinyl chloride)
Quantity Per Package	42 m
Operating Temperature	-15...60 °C
Length	2100 mm
Height	20 mm
Width	12 mm

### Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	2 cm
Package 1 Length	100 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	150 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	40
Package 2 Height	5.6 cm
Package 2 Width	12.5 cm
Package 2 Length	213 cm
Package 2 Weight	6.3 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	2160
Package 3 Height	54 cm
Package 3 Width	120 cm
Package 3 Length	220 cm
Package 3 Weight	360 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations