

Product data sheet

Specifications



OptiLine 45 - pole - tension-mounted - one-sided - polar white - 3500-3900 mm

ISM20105P

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	OptiLine
Product Name	OptiLine 45
Cabling Installation System	Pole
Product Type	Pole
Type Of Pole	One-sided
Pole/Post Surface Finish	Powder coated
Pole Fixing Mode	Tension-mounted

Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	Polar white (RAL 9003)
Front Opening Size	45 mm
Material	Aluminium powder coated
Quantity Package 1 / Unit	Set of 1
Height	3500...3900 mm
Depth	89 mm
Width	68 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	390.0 cm
Package 1 Width	6.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.9 cm
Package 1 Weight	8.97 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	1
Package 2 Height	12.7 cm
Package 2 Width	15.5 cm
Package 2 Length	363.5 cm
Package 2 Weight	9.464 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	28
Package 3 Height	64.9 cm
Package 3 Width	120.0 cm
Package 3 Length	370.0 cm
Package 3 Weight	285.992 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations