

# Product data sheet

Specifications



## OptiLine 45 - pole - tension-mounted - two-sided - polar white - 3500-3900 mm

ISM20111P

### Main

Range	OptiLine
Product Name	OptiLine 45
Cabling Installation System	Pole
Product Type	Pole
Type Of Pole	Two-sided
Pole/Post Surface Finish	Powder coated
Pole Fixing Mode	Tension-mounted

### Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	Polar white (RAL 9003)
Front Opening Size	45 mm
Material	Aluminium powder coated
Quantity Package 1 / Unit	Set of 1
Height	3500...3900 mm
Depth	90 mm
Width	116 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	390.0 cm
Package 1 Width	11.6 cm
Package 1 Length	9.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	13.81 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	1
Package 2 Height	12.7 cm
Package 2 Width	15.5 cm
Package 2 Length	363.5 cm
Package 2 Weight	14.306 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	28
Package 3 Height	64.9 cm
Package 3 Width	120.0 cm
Package 3 Length	370.0 cm
Package 3 Weight	421.568 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations