


# Product data sheet

Specifications



## TAP OFF UNIT FUPACT FUSE 200A GG LOW DISSIPATION

KH025SE351

⚠ Discontinued on: Apr 4, 2023

⚠ Discontinued

### Main

Range Of Product	Canalis
Range Compatibility	Canalis KT busbar trunking Canalis KH busbar trunking
Product Or Component Type	Tap-off unit
Busbar Trunking Compatibility	Canalis KT busbar trunking with KH type plug-in Canalis KHF and KGF busbar trunkingplug-in
[Ie] Rated Operational Current	250 A
Protection Type	Fupact INF switch-disconnector fuse: DIN fuse, size 1 - 250 A conforming to DIN 43653
Provided Equipment	switch-disconnector
Mounting Mode	Plug-in with auto-clamping system
Tap-Off Unit Polarity	3L+PEN

### Complementary

Device Application	Medium power distribution
[Ue] Rated Operational Voltage	690 V
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	800 V
Network Frequency	50/60 Hz
Control Type	Rotary handle
Standards	IEC 61439-1 IEC 61439-6
Colour	White (RAL 9001)
Width	700 mm
Depth	590 mm
Height	569 mm

### Environment

Earthing System	TN-C
Ip Degree Of Protection	IP43 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	69.0 cm
Package 1 Width	71.0 cm
Package 1 Length	85.0 cm
Package 1 Weight	82.0 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>