

Product data sheet

Specifications



Mounting plate, Linergy BZ, Platine Compact NSX 400-630 3P IEC/UL for 60 Busbars Interaxis

LV432623

Main

Range	Linergy
Product Name	BZ
Device Short Name	LA9Z
Product Or Component Type	Adaptors for busbar systems
Number Of Ways	1 way

Complementary

Range Compatibility	Prisma G Prisma P Prisma PH Spacial ComPact
Product Compatibility	NSX400...630 PowerPact NL
Poles Description	3P
Permissible Current	200 A - busbar cross section: 12 x 5 mm 250 A - busbar cross section: 15 x 5 mm 320 A - busbar cross section: 20 x 5 mm 400 A - busbar cross section: 25 x 5 mm 450 A - busbar cross section: 30 x 5 mm 360 A - busbar cross section: 12 x 10 mm 520 A - busbar cross section: 20 x 10 mm 630 A - busbar cross section: 30 x 10 mm
[Ui] Rated Insulation Voltage	690 V
Busbar Pitch	60 mm
Width	139 mm
Height	270 mm
Depth	63 mm
Colour	Anthracite grey

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
-------------------------	------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	14.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	31.500 cm
Package 1 Weight	2.076 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	13.281 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	24
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	63.140 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations